BURNDY

# YSV4CLNK, Uninsulated Splice, 4 AWG, Seamless, Nickel



By Burndy
Catalog # YSV4CLNK

Uninsulated Butt Splice, 4 AWG, Seamless, Electrolytic copper, Nickel Plated, Wire Stop, Bulk Package

## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size indentification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion
- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service

## Specifications

| | |
|---|---|
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus | No |
| UL Listed | No |
| Certification - CSA Approved | No |

## Conductor

| | |
|---|---|
| Conductor Size | 4 AWG |
| Conductor - Copper Str Aircraft Size | AN 4 |
| Conductor Type | • CU C Str-Size<br>• CU C Solid-Size<br>• CU C Str Aircraft-Size |

## Configuration

| | |
|---|---|
| Connector Type | Seamless Butt Splice |

## Current

| | |
|---|---|
| Voltage - Maximum | 600 V |

## Dimensions

| | |
|---|---|
| Package Height | 0.000 in |
| Dimension - B Length fraction | 1/2 in |
| Package Weight | 0.000 lb. |
| Package Length | 0.000 in |
| Package Width | 0.000 in |
| Dimension - L Length Overall mm | 28 mm |
| Dimension - B Length inch | 0.50 in |
| Dimension - Outside Diameter inch | 0.38 in |
| Dimension - Inside Diameter inch | 0.28 in |
| Dimension - Length Overall inch | 1.12 in |
| Dimension - Strip Length inch | 5/8 |

## General

| | |
|---|---|
| Feature - Barrel Style | Chamfered |
| Plated | Yes |
| Product Family | COMPRESSION |
| Trade Name | HYLINK™ |
| Die Index | 40 |
| Product Type | Splice |
| UPC | 781810050095 |
| Type | Splice |
| Material | Copper |
| Plating Type | Nickel |
| UPC 12 Digit | 781810050095 |
| UPC 14 Digit GTIN | 00781810050095 |

## Logistics

| | |
|---|---|
| Minimum Pack Quantity | 200 |
| Pallet Quantity | 99000 |
| Carton Quantity | 200 |

## Product Assets

Catalog [English]



© 2026 Hubbell Incorporated. All rights reserved


Downloaded from Arrow.com.