

 [PRODUCTS](#) ▾

 [DISTRIBUTOR INVENTORY](#)

 [INDUSTRIES](#) ▾

 [SUPPORT](#) ▾

 [NEWS & EVENTS](#) ▾

 [ABOUT US](#) ▾

SDX30A2

[Products](#) > [Sensors](#) > [Pressure Sensors & Transducers](#) > [Board Mount Pressure Sensors](#) > [Unamplified](#) > [SDX Series](#)
> [SDX30A2](#)

Overview

SDX Series, Absolute; Temperature Compensated Sensor, "A2" Package - Straight Port.

The SDX series sensors provide a very cost effective sol...



[View More](#)

 [view all SDX30A2 literature](#)

 [view distributor inventory](#)

 [sample request](#)

 [email support](#)

 [get support](#)

 [email sales](#)

 [find a distributor](#)

 [email this page](#)

Technical Specifications

Series Name	SDX	Measurement Type	Absolute
Signal Conditioning	Unamplified	Temperature Compensation	Yes
Pressure Range	0 psi to 30 psi	Supply Voltage	20 Vdc max.
Output Calibration	Yes	Response Time	100 µs
Port Style	Straight	Package Type	A2/G2 DIP

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 SDX Series Pressure Sensors (Compensated, DIP Package 0 to 1 psi up to 0 to 100 psi)	Datasheet	English	173KB
 Airflow, Force, and Pressure Sensors Range Guide	Product Range Guide	English	9MB
 Board Mount Pressure Sensors Line Guide	Product Line Guide	English	181KB
 Board Mount Pressure Sensors Selection Guide	Selection Guide	English	343KB

[View More](#)

Product Features

- Low Cost DIP
- Precision Temperature Compensation
- Calibrated Zero & Span
- Small Size
- Low Noise
- High Impedance for Low Power Applications
- Prime Grade Available (SDXxxxxy-A)

Applications

- Medical Equipment

- Computer Peripherals
- Pneumatic Controls
- HVAC

NAVIGATION LINKS[HOME PAGE](#)[PRODUCTS](#)[DISTRIBUTOR INVENTORY](#)[INDUSTRIES](#)[SUPPORT](#)[NEWS & EVENTS](#)[ABOUT US](#)**DISTRIBUTOR LINKS**[ECOM LOGIN](#)[LEARN CENTER](#)[REQUEST ACCESS TO ECOM](#)[SALES/AD PORTAL LOGIN](#)[SALES/AD PORTAL ACCESS REQUEST](#)[SAMPLE REQUEST](#)[SUPPLIER MICROSITE](#)**LANGUAGE** **SOCIAL MEDIA****SITE INFORMATION**[PRIVACY STATEMENT](#)[SITEMAP](#)[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.