



Part Number : [16020082](#)

Product Description : SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel

Series Number : 70058

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 70058-0006

Packaging Alternative : [16020097](#) (Bag)



Documents and Resources

Drawings

[016020082 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[PS-70058-001.pdf](#)

[PS-70400-001.pdf](#)

[TS-70058-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	70058
Description	SL Crimp Terminal, Series 70058, Female, 30-24 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	CyClone,SL
UPC	800753595996

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	114.800/mg
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	2.000µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size (AWG)	24, 26, 28, 30
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	<u>70066</u>
SL Dual Row Crimp Housings	<u>70450</u>

Application Tooling

Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	<u>11020022</u>
Extraction Tool for SL Terminals, 36-22 AWG	<u>11030036</u>
Hand Crimp Tool for SL Crimp Terminals, 30-24 AWG	<u>2002187000</u>
FineAdjust Applicator for SL Female Crimp Terminal, Insulation OD 0.63-1.00mm, 30-24 AWG Wire	<u>639001500</u>
FineAdjust Applicator for SL Female Crimp Terminal, Insulation OD 1.01-1.52mm, 30-24 AWG Wire	<u>639003100</u>

Japan

Description	Part Number
Hand Insertion Tool	<u>570336000</u>

This document was generated on Apr 24, 2026