



Barrel Terminals

**.030 [0.76] Max.
Aluminum Foil Thickness**
Related Product Data:
Application Tooling — page 9
Technical Documents — page 1



Type 1
Double Face



Type 2
Double Face
(Slotted)

Material and Finish	Type	Wire Barrel Range		Dimensions		Terminal Part Number	Foil Crimp Tooling	
		AWG	mm ²	T	L Max.		Hand Tool	Dies for Pneu. Tool 69010 with Head 69263-1
Nickel Plated Copper	1	16-14	1.25-2.0	.408 10.36	.671 17.04	329860	68026	69177-1
	1	12-10	3.0-6.0	.408 10.36	.781 19.84	329254		
	2	16-14	1.25-2.0	.708 17.98	.989 27.13	52195		
	2	12-10	3.0-6.0	.708 17.98	1.068 27.12	330716		
Tin-Plated Copper	1	16-14	1.25-2.0	.408 10.36	.671 17.04	329860-1	68026*	69177-1
	1	12-10	3.0-6.0	.408 10.36	.781 19.84	2-329254-4		
	2	12-10	3.0-6.0	.708 17.98	1.068 27.13	1-330716-2		
	2	12-10	3.0-6.0	.708 17.98	1.068 27.13	1-330716-3**		
	1	12-10	3.0-6.0	.932 23.67	1.296 32.97	330003		
	1	12-10	3.0-6.0	2.635 66.93	3.000 76.2	330005		
	1	8	7.0-8.0	3.549 90.14	3.979 101.07	50682		

*For heavy duty, use tool **68064**.

**Oblong wire barrel.

Wire Barrel Crimp Tooling

Wire Range		Hand Tool	Dies for Pneu. Tool	
AWG	mm ²		69005	69010
16-14 & 12-10	1.25-2.0 & 3.0-6.0	49935	300454	300583
8	7.0-8.0	69355	—	38394

Note: This is only a partial listing of tools that are available for crimping wire barrels. For additional tooling information call the AMP Customer Service Hotline **1-800-722-1111**.