



**Part Number :** 1301380081  
**Product Description :** Watertite Multiple Outlet Pendant Box, (2) NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip  
**Series Number :** 130138  
**Status :** Active  
**Product Category :** Power Distribution  
**Engineering Number :** 70W33M123



## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Relevant

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Power Distribution
Series	130138
Description	Watertite Multiple Outlet Pendant Box, (2) NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Watertite
Type	Multiple Outlet Box
UPC	78678840982

## Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	N/A

## Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	4.57m (15.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Net Weight	412.000/g
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

---

This document was generated on Apr 22, 2025