

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040049](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Haztex® Incandescent Hazardous and Wet Location Hand Lamp, 100W, 16/3 SOOW Cord Type, Cord Length 30.48m (100.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR39801
UL E30252

General

Product Family Portable Lighting
Series [130104](#)
Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)

NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Specialty Lighting](#)
Product Literature Order No 987650-8052
Product Name Haztex®
Type Hand Lamps, Specialty Light
UPC 78678861439
Woodhead Yes

Physical

Cord Length - Primary 30.48m (100.0')
Cord Length - Secondary N/A
Depth 127.00mm (5.000")
Duty Hazardous, Wet Location
Guard Included No
Guard Type N/A
Height 419.10mm (16.500")
Length N/A
Material - Globe Tempered Soda-Lime Glass
Material - Guard Cast Aluminum
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 61430D163



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
ELV Not Reviewed

Search Parts in this Series

[130104](#) Series

This document was generated on 07/06/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION