



**Part Number :** [1300950124](#)

**Product Description :** Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.406m (16.00"), Approximate Break Strength 2510.12kg (5600 lbs)

**Series Number :** 130095

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 35865



---

## Documents and Resources

### Drawings

[1300950124\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.406m (16.00"), Approximate Break Strength 2510.12kg (5600 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835865

#### Agency

CSA	LR32159
-----	---------

#### Physical

Approximate Break Strength	2510.12kg (5600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-15.49mm (.500-.610")
Color - Grommet	N/A
Eye Diameter	7/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.406m (16.00")
Net Weight	279.002/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

---

This document was generated on May 25, 2026