






used for: D-SUB COMBINATION CRIMP



NOTES:

1. METALSHELLS: STEEL; min. 320µin TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK

3. CONNECTOR IS PART MARKED: 3005W1PXK99A10X CONEC ABC

**Directive 2002/95/EC
„RoHS“
Compliant**

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
				2005	date	name	
				drawn	07.04.	Lehmenkühler	
				appd.	07.04.	Mickenbecker	
				norm			
				d-old			
							
rev.	description	date	name				



scale:	2:1 (5:1)		
material:	SEE NOTES		
title:	D-SUB COMBINATION MALE 5W1P CRIMP STYLE		
dwg no:	AutoCAD 2004	DIN-A	
13K1A1334		3	
		sh: 1/1	
part no: 3005W1PXK99A10X			