







Copyright FCI.



Part Number & Date Code Printing

LF FOR LEAD FREE

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	TIN LEAD P/N	LEAD FREE P/N
09	30.81	24.99	16.96	16.21	D09S13B6UA00	D09S13B6UA00**
15	39.14	33.32	25.18	24.54	D15S13B6UA00	D15S13B6UA00**
25	53.03	47.04	39.12	38.25	D25S13B6UA00	D25S13B6UA00**
37	69.32	63.50	55.68	54.71	D37S13B6UA00	D37S13B6UA00**

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

rev	ecn no	dr	date
C	I05-0124	JS	2005/07/27
D	I06-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOHN SLEEBA	1996/02/12	ANGULAR LINEAR		0.X	±0.1	size A3	Scale 1:1		
Eng	GEORGE VJ	1996/02/12			0.XX	±0.1				
Chr	GEORGE VJ	2005/07/27			0.XX° ±1°	0.XXX			±0.1	
Appr	KVSD	2005/07/27	Product family			D-SUB	Spec ref -			
		title	SOCKET CONNECTOR DELTA D				dwg no	C01-8646-0424		Rev. D
			RA WITH METAL PLATE							
			catalog no							
			DELTA-D				CUSTOMER	sheet 1 of 1		

REV F - 2006-04-17