




Part Number : [2070170010](#)

Product Description : Mini-Fit Sigma Sealed Plug Housing, Dual Row, 4.20mm Pitch, 10 Circuits, UL94V-0, Natural

Series Number : 207017

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 2070170010_sd.pdf](#)

[Packaging Design Drawing 2070170000-PK-000.pdf](#)

3D Models and Design Files

[3D Model 2070170010_stp.zip](#)

Specifications

[Application Specification 2070170000-AS-000.pdf](#)

[Product Specification 2070170000-PS-000.pdf](#)

[Test Summary 2070170001-TS-000.pdf](#)

[Test Summary 2070170000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	207017
Description	Mini-Fit Sigma Sealed Plug Housing, Dual Row, 4.20mm Pitch, 10 Circuits, UL94V-0, Natural
Application	Power, Wire-to-Wire
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma Sealed
UPC	193264428526

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	10
Color - Resin	Natural
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.000/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.20mm

Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Receptacle Housings	<u>46992</u>
Mini-Fit Jr. Receptacle Housings	<u>5557</u>
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	<u>172708</u>

Use with Part(s)

Description	Part Number
Mini-Fit Sigma Sealed Cap for 10 Circuit Plug Housing	<u>2070190010</u>
Mini-Fit Sigma Terminal Position Assurance (TPA) Retainer, 4.20mm Pitch, UL 94V-0, Glow-Wire Capable, 5 Circuits, Natural	<u>1727092005</u>
Mini-Fit TPA2/Sigma Male Crimp Terminals	<u>172765</u>
Mini-Fit TPA2/Sigma Male Crimp Terminals	<u>203070</u>

This document was generated on Sep 26, 2024