


Technical data sheet

Article number:
111-00698

T30R



Product Group	Cable Ties for higher chemical resistance for temperatures up to +170 °C in Ethylentetrafluorineethylene
Product Family	T-Series in E/TFE (Tefzel®)
Material	Ethylene Tetrafluoroethylene (E/TFE)
Colour	Blue (BU)
Application Range	High Temperature Environments
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	36.0 mm
Bundle Ø min.	3.0 mm
Flammability	UL 94 V0
Length (L)	150.0 mm
Min.Tensile Strength	133.3 N
Operating Temperature	-80 °C to +170 °C
Package Content	100 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 1565, ANSI/UL 62275
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64962
UV-Stabilised	Yes
Variant	Inside Serrated
Weight/Unit	0.001151 kg
Width (W)	3.5 mm

