



Heat shrinkable tubing 2:1 - Self extinguishing

TCN20

TCN20 is suitable for a wide range of applications like electrical insulations, mechanical protection and cable bundling.

Features and benefits

- Thin wall general purpose polyolefin tubing
- Highly flame-retardant, UL224 VW-1, CSA
- Fast shrinking
- Low shrink temperature



Heat shrink tubing TCN20.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	2:1
Operating Temperature	-55 °C to +125 °C
Min. Shrink Temperature	+100 °C
Longitudinal change after shrinkage	+/-5 %
Dielectric Strength	20 kV/mm according to IEC 243
Flammability	self-extinguishing



Heat Shrinkable Tubing 2:1

RoHS ✓

TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Tools	Article-No.
TCN20-1.2/0.6	1.2	3/64 "	0.6	0.30	300 m	Black (BK)	30-32	300-73010
TCN20-1.6/0.8	1.6	1/16 "	0.8	0.35	300 m	Black (BK)	30-32	300-73020
TCN20-2.4/1.2	2.4	3/32 "	1.2	0.45	300 m	Black (BK)	30-32	300-73030
TCN20-3.2/1.6	3.2	1/8 "	1.6	0.45	300 m	Black (BK)	30-32	300-73040
TCN20-4.8/2.4	4.8	3/16 "	2.4	0.50	300 m	Black (BK)	30-32	300-73050
TCN20-6.4/3.2	6.4	1/4 "	3.2	0.55	300 m	Black (BK)	30-32	300-73060
TCN20-9.5/4.8	9.5	3/8 "	4.8	0.55	100 m	Black (BK)	30-32	300-73070
TCN20-12.7/6.4	12.7	1/2 "	6.4	0.65	100 m	Black (BK)	30-32	300-73080
TCN20-19.1/9.5	19.1	3/4 "	9.5	0.80	60 m	Black (BK)	30-32	300-73090
TCN20-25.4/12.7	25.4	1 "	12.7	0.90	60 m	Black (BK)	30-32	300-73100
TCN20-38.1/19.1	38.1	1-1/2 "	19.1	1.02	30 m	Black (BK)	30-32	300-73110
TCN20-50.8/25.4	50.8	2 "	25.4	1.15	30 m	Black (BK)	30-32	300-73120

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools

	30	31	32
	H5002	H5004	E4500
	611	611	610

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.