



Part Number : [1301460150](#)

Product Description : Watertite Extreme Extra Hard Outdoor Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V, Black

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Part Number : 65W47BLK



Documents and Resources

Drawings

[1301460150 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Extra Hard Outdoor Receptacle with Single Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V, Black
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678831085

Agency

UL	E68122
----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
-----------	-----

Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Jun 02, 2026