

SEK CAB FLAT STD AWG28/7 60P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 060 7001
Specification	SEK CAB FLAT STD AWG28/7 60P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180607001

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

Version

Cable length	30.48 m
Number of cores	60
Core structure	AWG 28/7

Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Insulation resistance @ 20 °C	$\geq 20 \text{ M}\Omega \times \text{km}$

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Net weight	3,720 g
Country of origin	Germany
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)