


DRAWING MADE IN AMERICAN PROJECTION

LTR	REVISION RECORD	ECN	DR	CHK	DATE
D1	ECO-09-022178		KK	AEG	SEP09

NUMBER
C-160783



3 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

1 FOR USE ON MINIATURE APPLICATORS;
LEFT - RIGHT FEED
2 FOR USE ON MINIATURE APPLICATORS;
AMP-O-MATOR APPLICATION ; LEFT-RIGHT FEED

160783-8	3	NICKEL-SILVER	NONE	1
160783-6		PH BRONZE	PRE-TINNED	2
160783-5		STEEL	PRE-NICKEL	1
160783-4		PH BRONZE	NONE	1
160783-3	3	PH BRONZE	PRE-TINNED	1

CUSTOMER COPY FOR REFERENCE ONLY

© 1978 BY AMP-HOLLAND N.V. ALL RIGHTS
RESERVED AMP PRODUCTS COVERED BY
PATENTS AND OR PATENTS PENDING.



AMP-HOLLAND N.V.
's-Hertogenbosch

WIRE RANGE	INSUL. RANGE	FIRST USED
0.1 - 0.2 mm 0.01 - 0.008 in.	0.1 - 0.2 mm 0.01 - 0.008 in.	

ORDER NO.	MATERIAL	PLATING
-----------	----------	---------

SCALE	SIZE	NO.	REV
-------	------	-----	-----

DATE	DATE	DATE	DATE
------	------	------	------

1/1	A	C-160783	D1
-----	---	----------	----

DATE	DATE	DATE	DATE
------	------	------	------

28.12.78			
----------	--	--	--

RECEPTACLE FOR 2.0 (0.079) MM PIN

AMP 1202-M