

[Passive Components](#) >
 [Resistors](#) >
 [Fixed Resistors](#) >
 [Surface Mount Resistors](#)

TLR 1206 1.0W R022 1% 50PPM 5K RL



✓ **ACTIVE**

[CGS](#) | [CGS TLR](#)

TE Part # **TLR2B10DR022FTDG**

TE Internal #: **2176165-8**

Resistor Type : **Current Sensing Resistor**

Number of Terminations : **2**

Size Code : **1206**

Packaging Method : **Taped & Reeled**

Tolerance : **1%**

 [Add to List](#) ▼

| [Similar Products](#)



ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▼

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

CAD Files

PCB Design

[SnapEDA](#)

3D PDF

 [3D_CVM_CVM_2176165-8_BA.pdf](#) 3D

Customer View Model

 [ENG_CVM_CVM_2176165-8_BA.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_2176165-8_BA.3d_igs.zip](#)

English

 [ENG_CVM_CVM_2176165-8_BA.3d_stp.zip](#)

English

Product Environmental Compliance

TE Material Declaration

 [ENG_PC_MD_2176165-8_A.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Resistor Type : **Current Sensing Resistor**

Size Code : **1206**

in

f

	Product Type : Fixed Resistor
Configuration Features	Number of Resistors : 1
Electrical Characteristics	Tolerance : 1% Resistance (Ω): .022 Power Rating (W): 1
Termination Features	Number of Terminations : 2 Termination Type : Solder
Mechanical Attachment	Mount Style : Surface Mount
Dimensions	Dimensions (mm): 3.2 x 1.6 x .6
Usage Conditions	Temperature Coefficient (ppm/°C): ±75
Packaging Features	Packaging Method : Taped & Reeled
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

> [Contact Product Support](#)

Also in the Series

| [CGS TLR](#)



Surface Mount Resistors (104)



Time Delay Relays (1)

Customers Also Bought



TE Part #
TLR2B10DR007FTDG
TLR 1206 1.0W R007
1% 50PPM 2K RL



TE Part #
TLR2B10DR004FTDG
TLR 1206 1.0W R004
1% 50PPM 2K RL



TE Part #
CPF0603B348RE1
CPF 0603 348R 0.1%
25PPM 1K RL



TE Part # LR2F300R
LR2 1% 300R

About TE Connectivity

Our Company

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of Sale

For Partners

Distributors

Suppliers

Customer Support

Email or Call Us

Find Authorized Distributors

What's New on TE.com

Product FAQs

CALL US

LIVE CHAT

United States

Select Country & Language

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Find Your Country/Region