



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Installation guide User manual
--------------------	-----------------------------------

Physical

Colour	Black
Depth	66 cm
Height	13 cm
Net weight	90.91 kg
Number of rack unit	3U
Width	43.2 cm

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Batteries & Runtime

Number of battery blocks per string	16
Number of battery free slots	0
Number of battery filled slots	4
Device mounting	Stand alone battery stack

Battery voltage	192 V
Battery type	Lead-acid battery
Additional information	Replace all batteries in operation together (UPS internal and external batteries) all-at-once
Number of battery replacement quantity	2

Packing Units

Package 1 Weight	101.36 kg
Package 1 Height	41.3 cm
Package 1 width	60 cm
Package 1 Length	100 cm
Number of Units in Package 3	4

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
----------	--