

Search...

SPC5742PK1AMLQ8 :Part Detail

General Information	Package Information	Environmental and Compliance Information	Manufacturing Information	Ordering Information
Operating Characteristics				

General Information

Part Number	SPC5742PK1AMLQ8
Description	1.5MB NVM, 2 x e200Z4 cores, 180MHz, 192K SRAM, 4 x ADC, 2 x PWM, 2 x SENT
Product Line	G9F5744P
PTI	JBSS
Material Type	Tested Packaged Device
Life Cycle Description (code) (/webapp/sps/site/eialink.jsp)	PRODUCT RAPID GROWTH
Status	Active
SafeAssure Functional Safety (http://www.nxp.com/about/about-nxp/technology-leadership/safeassure-functional-safety-program:SAFETYPRGRM)	ISO 26262
Application/Qualification Tier (/webapp/sps/site/aqmlink.jsp?type=pop_up)	AUTO; >=10 YEARS APPLICATION LIFE

Package Information

Package Type and Termination Count	LQFP 144
Package Description and Mechanical Drawing	LQFP 144 20SQ1.4P0.5 C90
Device Weight(g)	1.31910
Package Length (nominal)(mm)	20.000
Package Width (nominal)(mm)	20.000
Package Thickness (nominal)(mm)	1.500
Maximum Height Above Board(mm)	1.600
Tape & Reel	No

Environmental and Compliance Information

Pb-Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PBFREE_INFO&type=pop_up)	
RoHS Compliant (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_INFO&type=pop_up)	
Halogen Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=HALOGEN_FREE_INFO)	Yes
Material Composition Declaration (MCD) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_MCD&type=pop_up)	Download MCD Report  (/mcds/SPC5742PK1AMLQ8.pdf) Download MCD Report  (/mcds/SPC5742PK1AMLQ8.xls)
RoHS Certificate of Analysis (CoA) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_COA&type=pop_up)	Contact Us (https://nxpcommunity.force.com/community/communityContactSupport)
2nd Level Interconnect (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PLATING_INDICATOR_INFO)	e3
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS

Peak Package Body Temperature (PPT)(°C)	260
Maximum Time at Peak Temperature (s)	40
Number of Reflow Cycles	3
REACH SVHC	NXP REACH Statement (/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf)
UL94 (plastics flammability test)	V0;Burning stops within 10 seconds on a vertical specimen;no drips allowed

Manufacturing Information

Micron Size(μm)	.05
-----------------	-----

Ordering Information

Minimum Package Quantity (MPQ)	60
MPQ Container	TRAY
Exempt from Minimum Delivery Value	Yes
Preferred Order Quantity (POQ)	600
POQ Container	BOX
Leadtime (weeks)	20
Export Control Classification Number (US)	3A991A2
Harmonized Tariff (US) Disclaimer (/webapp/sps/site/harmTariffDisclaim.jsp)	8542.31.0000
CCATS Document	-
ENC Status	-
Other Trade Compliance Documents	-
Budgetary Price excluding tax(US\$) (/webapp/sps/site/bplink.jsp) Change Currency	-
Order	

Operating Characteristics

Sample Exception Availability	N
-------------------------------	---

ABOUT NXP

Investors (<http://investors.nxp.com/phoenix.zhtml?c=209114&p=irol-irhome>)
Partners (<http://www.nxp.com/webapp/connect/memberDirSearch.sp>)
Careers (<http://www.nxp.com/about/careers-at-nxp:CAREERS>)

FOLLOW US

(<https://twitter.com/NXP>) (<http://www.linkedin.com/company/nxp-semiconductors>) (<https://www.facebook.com/NXPsemi>)

(<https://contact.nxp.com/Subscription-Center>)

News 16 Feb 2017

NXP Wins Prestigious Automotive Innovation Award with Radar
Read More (<http://phx.corporate-ir.net/phoenix.zhtml?c=254228&p=irol->

RESOURCES

Mobile Apps (<http://www.nxp.com/about/nxp-mobile-applications:MOBILE>)
Press, News, Blogs (<http://media.nxp.com>)
Contact Us (<http://www.nxp.com/pages/contact-us:CONTACTUS>)

