

Product data sheet

Characteristics

PBCE4A225AST120B

PB Busway Straight Distribution, 10ft, 225A, 600V max



Overview

Description	Totally enclosed bus bar conductors with finger-safe plug-in openings. Outlets directly above racks ensure flexibility when you need to move, add, or change a branch circuit. Spring-joint connectors simplify installation and reduce maintenance requirements. No special tools required for installation.
Model Name	PB Busway Straight Distribution, 10ft, 225A, 600V max
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada , United States

Output

Maximum Total Current Draw per Phase	225 A
--------------------------------------	-------

Input

Nominal Input Voltage	208 3PH 415 3PH 600 3PH
Input Frequency	60 Hz

Physical

Net Weight	23.18 kg
Maximum Height	176.0 mm
Maximum Width	3048.0 mm
Maximum Depth	88.0 mm
Shipping Weight	43.64 kg
Shipping Height	97.0 mm
Shipping Width	3200.0 mm
Shipping Depth	196.0 mm
Color	Black

Environmental

Operating Environment	-10 - 40 °C
Operating Relative Humidity	0 - 95 %

Jun 14, 2020

Operating Elevation	0-3000 meters
Storage Temperature	-30 - 70 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-4500 meters

Conformance

Approvals	CSA , UL Listed , cUL Listed
Standard warranty	1 year (parts only)

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs