

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0982670250
Status: Active
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 10 Circuits



Series image - Reference only

Documents:

- Drawing (PDF)
- Product Specification PS-98267-001-001 (PDF)
- Datasheet (PDF)
- RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Cable

98267

Contacts on opposite sides, Type D

Yes

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Premo-Flex FFC Jumper

756054770801

Physical

Cable Length

Circuits (Loaded)

Contact Layout Type

Material - Plating Mating

Net Weight

Packaging Type

Pitch - Mating Interface

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

76.00mm

10

D (opposite side)

Tin

0.584/g

Bag

1.00mm

-40° to +105°C

N/A

Flat Flex Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.2A

60V AC

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-98267-001-001

SD-98267-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

98267 Series

Mates With

Easy-On FFC/FPC Connector:

[522071033](#) , [522711079](#) , [526101033](#) ,
[526101034](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION