

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-RLCATALOG LISTING
BZ-RL
PAGE 1 OF 1**M**ISSUE
13

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO5200	LLD	20 MAR 64
B	CO23645	MBF	22 JAN 68
C	CO46304		
J	A P		12 OCT 79
D	CO	58037	
	SMA		1 OCT 85
E	CO-78874		
	DLT		17 NOV 94
F	CO-94212-J		
	J J A		5 OCT 99
G	203222		
	CSL		5 JUN 01

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 3 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

DIFFERENTIAL TRAVEL ----- .030 MAX

DO NOT OVERTRAVEL MORE THAN --- .060

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

L103

15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VACL288
L299
L306

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT .050 LB

RASTER

FO-50378

DRAWN

20 MAR 64

21 MAR 64

21 MAR 64