# USB-C to Mini DisplayPort Active Adapter Cable (M/M), 4K 60 Hz, Black, 6 ft. (1.8 m)

MODEL NUMBER: **U444-006-MDP**







Connects your existing Mini DisplayPort (mDP) monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC. Saves you the clutter and expense of additional cables, adapters and displays.

## Features

**Connects a Mini DisplayPort Display to Your USB-C or Thunderbolt 3 Device**Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate ModeIdeal for giving video presentations, editing multiple documents, or streaming 4K video for digital signageSupports USB 3.1 Gen 1 data transfer rates up to 5 GbpsSupports DisplayPort 1.2 specificationsExtend 4K video from your primary display to another, duplicate the same video on both, or convert a secondary display to be the primary display

**Crystal-Clear 4K Video and Digital Audio**Supports UHD video resolutions up to 3840 x 2160 (4K) @ 60 HzSupports 36-bit Deep Color (12 bits per channel)Supports per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)

**Reversible USB-C Connector**Fumble-free reversible USB-C plug connects in either direction for quick connection every time

**Premium Construction**Gold-plated connectors and contacts for maximum conductivity and minimum data lossFoil and braid shielding protects against EMI/RFI line noise that can distort or destroy dataIntegral strain relief helps cable and connectors move freely without stress or crackingDurable PVC jacket designed to last a long time

**Ready for Instant Use**Plug-and-play operation with no software, drivers or external power required6 ft. length easy to manage in crowded environmentsBackward compatible with non-4K displays

## Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 4K @ 60 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

## System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with Mini DisplayPort input

## Package Includes

- U444-006-MDP USB 3.1 Gen 1 USB-C to Mini DisplayPort 4K Adapter Cable (M/M), 6 ft.

# Specifications

| OVERVIEW | |
|---|---|
| UPC Code | 037332193841 |
| Product Type | Active Cable |
| Technology | DisplayPort |



Downloaded from Arrow.com.

| | |
|---|---|
| Cable Type | Active |
| **VIDEO** | |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 60Hz |
| HDR Support | Yes |
| **INPUT** | |
| Bus Powered | Yes |
| Product Length (in.) | 72 |
| Product Length (cm.) | 182.88 |
| Product Length (ft.) | 6 |
| Product Length (m) | 1.83 |
| **BATTERY** | |
| Battery Charging (5V/1.5A Port) | No |
| **POWER** | |
| Power Consumption (Watts) | 0.6 |
| **CONNECTIONS** | |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | MINI DISPLAYPORT (MALE) |
| Connector Plating | Gold |
| **PHYSICAL** | |
| Color | Black |
| Material of Construction | PVC, ABS |
| Cable Jacket Color | Black |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.19 |
| Shipping Weight (kg) | 0.09 |
| Unit Dimensions (hwd / in.) | 9.000 x 7.000 x 0.500 |
| Unit Packaging Type | Polybag |



Downloaded from Arrow.com.

| | |
|---|---|
| Unit Weight (lbs.) | 0.18 |
| Unit Weight (kg) | 0.08 |
| **ENVIRONMENTAL** | |
| Operating Temperature Range | 32° to 113°F (0° to 45°C) |
| Storage Temperature Range | 14° to 158°F (-10° to 70°C) |
| BTUs | 2.1 BTU/Hr |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| **FEATURES & SPECIFICATIONS** | |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| IP68 Rated | No |
| IP20 Rated | No |
| UASP Support | No |
| Auto MDIX Support | No |
| Full Duplex Support | No |
| Suspend Mode Support | No |
| Remote Wakeup Support | No |
| Displayport Specification | 1.2 |
| HDCP Specification | 1.3 |
| Driver Required | No |
| **STANDARDS & COMPLIANCE** | |
| Product Compliance | CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE |
| **WARRANTY & SUPPORT** | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.



Downloaded from Arrow.com.