



SEK 10P female connector

SEK 10P female connector

TOLERANCE FOR "L" LENGTH

DIMENSION RANGE	TOLERANCE
0.0m - 1.0m	+10/0 mm
>1.0m - 3.0m	+30/0 mm
>3.0m - 5.0m	+50/0 mm
>5.0m - 10.0m	+100/0 mm
>10.0m	+200/0 mm

NOTES:

- 1) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
- 2) WHITE LABEL CONTENT:

CMK/YR-XXXX-X-XX
HARTING P/N

BLACK FONT, FONT HEIGHT: 3.5.

- 3) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).
- 4) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

33 18 243 100 0067	1 m	Tech Character.	Free size tolerances
33 18 243 080 0066	0.8 m		
33 18 243 050 0065	0.5 m		
33 18 243 020 0064	0.2 m		
33 18 243 010 0063	0.1 m	Port-No.	Dim.L
All dimensions in mm Original Size DIN A 3			
		Tech Character.	
		Det.	How
		Detail	03/07/08 Aaron
		Imp.	
		Stand	
		Scale	
		/	
		SEK 10P FEMALE DOUBLE END FLAT CABLE ASSEMBLY L=xM	
		TB 33 18 243 xxx 00xx	
		Page	
Mod.	Doc.	Name	
ZHAHAI HARTING LIMITED			
S&B			