



Part Number : [732510250](#)
Product Description : SMA Jack, Straight, 2-Hole
Flange Mount, Solder Cup Contact, Stainless Steel
Body, Passivated, 50 Ohms
Series Number : 73251
Status : Active
Product Category : RF / Coaxial Connectors

Documents and Resources

Drawings

[732510250_sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	SMA Jack, Straight, 2-Hole Flange Mount, Solder Cup Contact, Stainless Steel Body, Passivated, 50 Ohms
Application	RF
Comments	Solder Pot
Product Name	SMA
Style	Panel
Type	Subminiature
UPC	756054576038

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.861/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Flange
PCB Mounting	N/A

Reverse Polar	No
Wire/Cable Type	0.79mm Coaxial max.

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Jul 04, 2026