

Product data sheet

Specifications



Rack Distribution Panel 208 V

PDRDPF10U-R

❗ End-of-service on: 04 February 2022

PDRDPF10U-R has not been replaced. Please contact your customer care center for more information.

❗ Discontinued

Overview

Lead time Usually Ships within 3 Weeks

Main

Main Input Voltage 208 V 3 phases

Main Output Voltage 120 V
208 V 3 phases

Plug standard IEC 60309

Number of rack unit 42U

Number of cables 1

Provided equipment Installation guide
User manual

Physical

Colour Black

Height 206 cm

Width 61 cm

Depth 107.2 cm

Net weight 190 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Network frequency 60 Hz +/- 3 Hz

Max line current 80 A

Load capacity 28800 VA

Conformance

Product certifications cUL listed
UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...9144.00 m

Packing Units

Package 1 Weight	200 kg
Package 1 Height	226.1 cm
Package 1 width	91.4 cm
Package 1 Length	121.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------