

RJ45 Punch Down Plugs

Cat 5e, Cat 6 and Cat 6a Ethernet Solutions

Stewart Connector's RJ45 punch down plugs are time-saving solutions for Ethernet connections that require field terminations. The applications for Stewart's RJ45 punch down plugs include data, telecom, wireless, PoE applications, and industrial equipment connections.





Features

- The RJ45 punch down plugs are designed for quick and easy field terminations
- The RJ45 punch down plugs can be disassembled for easy rework
- The Cat 6 punch down plug is suitable for use in 1GBASE-T networks and the Cat 6a for 10GBASE-T networks
- Contact designed for use on solid or stranded conductor cable
- 50 micro-inches of gold plating on contacts for increased cycle life
- Terminates 23-26 AWG cable

Benefits

- Compression strain relief
- No termination tooling required
- Adequate for Power Over Ethernet applications
- FTP Plugs utilize robust zinc die-cast housings
- Each plug kits includes termination instructions
- Easy to use color coded conductor pre-load wire manager

Part Numbers

Part Number	Performance	Shielding	Wire Guage	Cable OD	
				mm	in
SS-39300-001	Cat 6	FTP	23-26 AWG	6-8mm	0.236-0.315in
SS-39300-002	Cat 6a	FTP	23-26 AWG	6-8mm	0.236-0.315in
SS-39300-013	Cat 5e	UTP	23-26 AWG	4-6mm	0.157-0.236in
SS-39300-014	Cat 6	UTP	23-26 AWG	4-6mm	0.157-0.236in

stewart CONNECTOR a bel group

Stewart Connector
11118 Susquehanna Trail South
Glen Rock, PA 17327-9199

+1 717.235.7512
techhelp@belf.com
belfuse.com/stewart-connector

© 2021 Stewart Connector

Please read our datasheet & drawing disclaimer here.

Downloaded from Arrow.com.