



Products

Customize Your Parts

Industries Solutions

Search

News & Events

First Time?



(0)



Home / Products / M Series / M12 (X)

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



MSXS-08PFFR-SH7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: UL1863

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

Specifications	Download / CAD
Nominal Current 0.5A	Connector Type Receptacle
Shielded Metal, Shielded	No. of Contacts 08
Connector Gender Female	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IP67
Assembly Style PCB 90°	
+ More Options	

People Also Bought