

Technical data sheet

Article number:
156-02468

T120RCPM6-TSSET

| | |
|----------------------------------|------------------------------------------------------------------|
| Product Group | 2-Piece Fixing Ties for Heavy Duty Applications, for Screws |
| Product Family | HDM-Series |
| Material | Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS) |
| Colour | Black (BK) |
| Bundle Ø max. | 105.0 mm |
| Bundle Ø min. | 5.0 mm |
| Cable Tie | Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS) |
| CE Certification | No |
| Fixation Method | Screw Mount |
| Flammability | UL 94 HB |
| for Hole Ø (FH) | 6.2 mm |
| Height (H) | 23.5 mm |
| Length (L) | 385.0 mm |
| Min.Tensile Strength | 535 N |
| Mounting Screw Type | M6 Screw |
| Operating Temperature | -40 °C to +110 °C |
| Package Content | 1000 pcs. |
| Package Content packed in | pack |
| ROHS compliant | Yes |
| Stud Ø | 6.0 mm |
| Thickness (T) | 1.8 mm |
| UV-Stabilised | No |
| Variant | Inside Serrated |
| Width (W) | 7.6 mm |

