

Johanson Part Number 7240BP15B2000001E

Johanson Part Number: 7240BP15B2000001E

Johanson Company: JTI

Legacy P/N: 7240BP15B2000E

Size for Capacitors (EIA): None

Description: Band Pass Filters, 805, 6240 -
8240MHz, 3W, 2.5dB, Ni/Sn (RoHS), UWB Band
Pass Filter, EIA 0805, High Rejection, 7" Reel
Embossed Tape

Specification Number: None

Life Cycle Stage: Active - Production

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.041

Schedule B: 8534

Thickness (Min): 0.033

ITAR: No

End Band(Min): 0.04

ECCN: EAR99

End Band (max): 0.055

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 14

Country of Origin: TW

Length (Min): 0.073

Product Family: Integrated Passive Components

Length (Max): 0.085

Product Subfamily: Band Pass Filters

Width (Min): 0.045

Capacitance Value: None

Width (Max): 0.053

Cap Unit of Meas: None

Part Weight (mg): None

Tolerance: None

Packaged Width (lb) Arm: None

Voltage: None

Packaging: 7" Reel Embossed Tape

Dielectric Temp Coefficient: None

Packaging Qty: 4000

Termination: 0

Operating Temp Range: -40°C to +85°C

Marking: Special

Storage Temp Range (Packaged): -40°C to +85°C

Product Release Date: April 29, 2020, 7 a.m.

Storage Temp Range (None Operating): +5°C to
+35°C with RH 45% to 75%

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansontechnology.com/band-pass-filters>

Printed from: www.johansontechnology.com/search/pn-detail/?s=7240BP15B2000001E