

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Mini
- Micro
- Accessory
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



HMC-000505-OMF-CSA02

Operating Temperature: -20°C ~ +80°C
Transmission Speed: N/A
Shielded: Metal, Non-shielded
Jacket Material: PVC
Certificate: NMEA 2000

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search



M Series...
CAP-WBDMSMA2
-40°C ~ +105°C

- 0 +

☐



NMEA 2000...
E-555500-...
-20°C ~ +85°C

- 0 +

☐



NMEA 2000...
E-555500-...
-20°C ~ +85°C

- 0 +

☐



NMEA 2000...
E-555500-...
-20°C ~ +85°C

- 0 +

☐



NMEA 2000...
E-555500-...
-20°C ~ +85°C

- 0 +

☐



NMEA 2000...
E-555500-...
-20°C ~ +85°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Overmolded
Shielded Metal, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Straight
Mating Style Screw Thread	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

