Specifications



Photo is representative

Eaton CPL2-5-50TR-R

Eaton CPL2 inductor, 50 nH, 10 A ISAT, 0.28 mΩ resistance, SMT mounting, Ferrite, 10-pins, Five-phase, 750 qty.

General specifications	
PRODUCT NAME	Eaton CPL2 inductor
CATALOG NUMBER	CPL2-5-50TR-R
UPC	051712235051
PRODUCT LENGTH/DEPTH	45 mm
PRODUCT HEIGHT	4.8 mm
PRODUCT WIDTH	8.5 mm
PRODUCT WEIGHT	2.87 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Five-phase
ISAT	10 A
PACKAGE QUANTITY	750
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	10-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.28 mΩ
INDUCTANCE	50 nH
SERIES	CPL2

Resources

SPECIFICATIONS AND DATASHEETS	Eaton CPL2 mutli phase power indcutors data sheet Eaton Specification Sheet - CPL2-5-50TR-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.