

Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 4 ft. (1.22 m), Yellow Plugs

MODEL NUMBER: **P006-004-YW**



Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 4-ft. (1.22 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer AC power cable features fully molded yellow ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332168498
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter
- NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable
- Yellow plugs for fast, easy identification in a crowded PDU, UPS or surge protector

Applications

- Connect devices like computers, printers and monitors to a PDU up to 4-ft. (1.22 m) away in your workstation
- Extend an existing power connection up to 4-ft. (1.22 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-004-YW NEMA 5-15P to C13 Computer Power Cable, 4-ft. (1.22 m), Yellow Plugs

Plug Color	Yellow
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	4
Cable Length (m)	1.22
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Storage Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Angled Plug	No
High Voltage	No
Locking Plug	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.