Data sheet

FBCON SS PCG 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	Standard distributor with bus termination (active), 1-way distributor, IP65, IP66, Round
Order No.	8613670000
Type	FBCON SS PCG 1WAY
GTIN (EAN)	4032248316960
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2025-11-30T00:00:00+01:00

Downloaded from Arrow.com.

Data sheet

FBCON SS PCG 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Depth	79 mm	Depth (inches)	3.1102 inch
Height	36 mm	Height (inches)	1.4173 inch
Width	58 mm	Width (inches)	2.2835 inch
Net weight	402 g		

Temperatures

Storage temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Operating temperature	-40 °C...80 °C	Humidity	5...95 %, no condensation

Probability of failure

SIL in compliance with IEC 61508	None

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

Connection data

Clamping range, min.	4 mm²	Clamping range, max.	6 mm²

Technical data

Number of poles	3	Cable glands	Plastic screwed cable gland
Connection type PE	all connectors with plastic cable gland	Type of distribution	1-way distributor
Design of housing	With pressure compensation element	Housing main material	Stainless steel, rust-proof, Aluminum
Cable entry	Round	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	6.5 mm	Type of mounting	surface-mounted
Protection degree	IP65, IP66	Pollution severity	3
Bus system	Profibus-PA, Foundation Fieldbus	Operating voltage	30 V
Housing surface	polished	Operating voltage Umax, max.	30 V DC

Classifications

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-44-01-11
ECLASS 15.0	27-44-01-11		


Downloaded from Arrow.com.


FBCON SS PCG 1WAY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings





Downloaded from Arrow.com.