Pushing Performance
Since 1945

UIC558-22PIN-MI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 022 3001
Specification	UIC558-22PIN-MI-CRT
HARTING eCatalogue	https://harting.com/09580223001

Identification

Category	Inserts
Series	HARTING UIC
Identification	UIC 558

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	22
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section (mm²)	0.75 ... 1 mm²
Conductor cross-section (AWG)	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	$>10^7$ Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	UIC 550
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	35.38 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140187009
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.