Littelfuse® | Carling Technologies®
A Littelfuse® Brand


LRG-Series

Illuminated Double Pole Rocker & Paddle Switches

PRODUCT WEBPAGE

request sample, configure part





The double pole lighted version of the R-Series incorporates the same sleek lines as the original Curvette, in a double pole envelope. This illuminated version features silver-plated butt-action contacts with ratings to 20A/125, 15A 250VAC and withstand peak inrush currents up to 100 amps. Clear or translucent style rocker actuators and a choice of solder lug, .250 Tab and wire lead terminations enable this switch to adapt to high current applications.

2	15-20	125-250	6-24
Poles	Amps	VAC	VDC

Typical Applications

- Power Supply
- Appliances
- Exercise Equipment
- Music Equipment

www.carlingtech.com 860.793.9281 sales@carlingtech.com

Downloaded from Arrow.com.

Tech Specs

Dielectric Strength

UL/CSA: 1000V - live to dead metal parts & opposite polarity

Electrical Life

100,000 cycles

Operating Temperature

-40°F to 185°F (-40°C to 85°C)

Ordering Scheme

Sample Part Number	LRGSCK611	-	R	S	-	B	-	B	/	250N
Selection	1		2	3		4		5		6

1. SERIES

15A 250 VAC, 20A 125 VAC, 3/4 HP 125-250 VAC

	Solder Lugs	.250 Tabs	Wire Leads
Standard Base			
OFF-NONE-ON	**LRGSCK610**	**LRGSCK611**	**LRGSCK615**
European Base (22 x 30 mm cutout)			
OFF-NONE-ON (Single Pole)	**LRGSEK610**	**LRGSEK611**	**LRGSEK615**
15A 6-24 V [3]			
Standard Base			
OFF-NONE-ON	**LRGSCK510**	**LRGSCK511**	**LRGSCK515**
European Base (22 x 30 mm cutout)			
OFF-NONE-ON (Single Pole)	**LRGSEK510**	**LRGSEK511**	**LRGSEK515**

2. ACTUATOR STYLE

R	Rocker translucent	**C**	Rocker Clear

3. ACTUATOR COLOR

A	Amber	**P**	Yellow
B [3,5]	Blue	**R**	Red (clear)
C [4]	White/Clear	**S**	Red
G [5]	Green	**W**	Pale Red
L [3]	Lime Green		

4. BEZEL COLOR

B	Black	**W**	White

5. ROCKER LEGEND

	hot stamp
NO LEGEND	**0**
OFF-ON vertical	**A**
OFF-ON horizontal	**B**
O-I horizontal	**D**
O-I vertical	**E**
Dual OFF-ON, O-I vertical	**H**
Dual OFF-ON, O-I horizontal	**J**

6. LAMP VOLTAGE


006V	6V incandescent	**024V**	24V incandescent
012V	12V incandescent	**125N**	125V neon
018V	18V incandescent	**250N**	250V neon


Notes:
1 Additional ratings, colors and clear style actuators are available. Consult factory.
2 Incandescent lamps must specify 15A 24V rating only.
3 Available with incandescent lamps only.
4 Clear color provided where specified with clear style rocker.
5 Available with clear style rocker only.


Configure Complete Part Number > Browse Standard Parts >

Dimensional Specs

inches [millimeters]







MOUNTING HOLE
Panel Thickness: .025 min - .187 max.
Specific cutout dimension range dependent on panel thickness and material.

*Manufacturer reserves the right to change product specification without prior notice.

Downloaded from Arrow.com.