

Part Number : [397000104](#)

Product Description : 5.08mm Pitch, Eurostyle Fixed-Mount Push-Button Terminal Block, 45° Modular, 18A, 26-14 AWG, Green, 4 Circuits

Series Number : 39700

Status : Active

Product Category : Terminal Blocks and Barrier Strip

Engineering Part Number : M508-00-04-3

Documents and Resources

Drawings

[397000104_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Terminal Blocks and Barrier Strip |
| Series | 39700 |
| Description | 5.08mm Pitch, Eurostyle Fixed-Mount Push-Button Terminal Block, 45° Modular, 18A, 26-14 AWG, Green, 4 Circuits |
| Application | Wire-to-Board |
| Component Type | One Piece |
| Product Name | Eurostyle Fixed Mount |
| Type | PCB Terminal Blocks and Connectors |
| UPC | 78172542426 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 18.0A |
| Voltage - Maximum | 300V |

Physical

| | |
|---------------------|-----------|
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Green |
| Entry Angle | 45° Angle |
| Lock to Mating Part | No |

| | |
|--------------------------------|----------------------------|
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Number of Rows | 1 |
| Orientation | 45° Angle |
| Panel Mount | Yes |
| Pitch - Mating Interface | 5.08mm |
| Polarized to Mating Part | No |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size (AWG) | 14, 16, 18, 20, 22, 24, 26 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

This document was generated on May 20, 2026