



**Part Number :** [1300970158](#)

**Product Description :** Deluxe Cord Grips Strain Relief, 3/4" NPT, Grip Body Size F3, Straight Male, Cable Diameter 19.05-22.23mm

**Series Number :** 130097

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 36248



---

## Documents and Resources


### Drawings

[1300970158 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(b) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130097
Description	Deluxe Cord Grips Strain Relief, 3/4" NPT, Grip Body Size F3, Straight Male, Cable Diameter 19.05-22.23mm
Hazardous Locations	Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
NEMA Rating	NEMA 4
Product Name	Deluxe Cord
Type	Strain Relief Grip
UPC	78678836248

#### Agency

CSA	LR32159
-----	---------

#### Physical

Approximate Break Strength	N/A
Bale Length	0.117m (4.63")
Body Style	Straight
Cable Diameter	19.05-22.23mm (.750-.875")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Aluminum
Material - Grip	Stainless Steel
Mesh Length	0.235m (9.25")
Net Weight	96.819/g

Number of Holes	N/A
O-Ring	N/A
Thread Size	3/4" NPT

## Mates With / Use With

### Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

---

This document was generated on May 24, 2026