



OCEAN APPLICATORS



✓ Active

TE CONNECTIVITY (TE)
OC-AT-S-FA-090F140O-001-0275
AMP

2151701-2
TE Internal Number: 2151701-2

Not in Scope for EU RoHS/ELV Compliance

Region **Worldwide**

Tool Type **Applicator**

Spare Parts Tooling **No**

Applicator Style **OCEAN - Atlantic**

Applicator Feed Style **Side Feed**

Product Drawings

[Ocean Side Feed Applicator](#)

PDF
English

Catalog Pages/Data Sheets

[4-1773460-5_New Series Of Applicators From](#)

PDF
English

Instruction Sheets

Instruction Sheet (U.S.)

[Ocean Side-Feed Applicators](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Tool Type	Applicator
Spare Parts Tooling	No
Applicator Style	OCEAN - Atlantic
Applicator Feed Style	Side Feed
Applicator Feed Type	Pneumatic

Product Availability

Region **Worldwide**

Product Compliance

[Statement of Compliance](#)
PDF

Products - 4 Results

View All

Compare 0/10

Relation Type

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

FLOATING SHEAR
- 318707-1

TE INTERNAL NUMBER: 318707-1

Active

Not in Scope for EU RoHS/ELV
Compliance

Region Worldwide

Tool Type Applicator

Spare Parts Tooling Yes

Spare Parts Tool Type Shear

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

ANVIL, COMBINATION
.090 - 1633132-9

TE INTERNAL NUMBER: 1633132-9

Active

Not in Scope for EU RoHS/ELV
Compliance

Region Worldwide

Tool Type Applicator

Spare Parts Tooling Yes

Spare Parts Tool Type Anvil

RELATIONSHIP

Spare Parts
Spare Parts

See All Spare Parts



PRODUCT - SPARE PARTS

Application Tooling - OCEAN Applicators
AMP

CRIMPER, WIRE .090 F
- 4-456406-7

TE INTERNAL NUMBER: 4-456406-7

Active

Not in Scope for EU RoHS/ELV
Compliance

Region Worldwide

Tool Type Applicator

Spare Parts Tooling Yes

Spare Parts Tool Type Crimper

