



Pushing Performance
Since 1945

Pneumatic Crimping Tool Set Han C/D/E



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0314
Specification	Pneumatic Crimping Tool Set Han C/D/E
HARTING eCatalogue	https://harting.com/09990000314

Identification

Category	Tools
Type of tool	Pneumatic crimping tool
Description of the tool	Han D [®] : 0.14 ... 2.5 mm ² Han E [®] : 0.14 ... 4 mm ² Han [®] C: 1.5 ... 4 mm ²
Type of drive	Pneumatic

Version

Die set	4-mandrel two-indent crimp
Direction of movement	4 indent
Field of application	Recommended for production lines up to 10,000 crimping operations per year
Pack contents	In plastic case Locator Han [®] C Locator Han E [®] Locator Han D [®] Adjustment gauge Pneumatic tube Operating instructions

Technical characteristics

Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	4,100 g
Country of origin	USA
European customs tariff number	84671900
GTIN	5713140106406
ETIM	EC000168
eCl@ss	21043811 Crimping pliers