



D

C

B

A



- PART NUMBER OF HOUSING TO BE MATE : SEE TABLE -1 TO BE MATED SMOOTHLY WITH THE PLUG HOUSING ASSEMBLY
- RECOMMENDED SCREW : PAN-HEADED TYPE 2 TAPPING SCREW, NOMINAL DIAMETER 3mm, LENGTH; SEE TABLE-3 (JIS B1115,B1122)
- FASTENING TORQUE FOR SCREW : 0.392N·m MAX

MEASURED AT 6 mm FROM -Z-
INSTRUCTION SHEET NO : 411-5928
APPLIED TERMINAL : SEE TABLE -2

IDENTIFICATION MARK FOR THE CONTACT FINISH ;
SEE TABLE

MEASURED AT 2 mm FROM -Z-

CIRCUIT NUMBER : SEE FIG.1

- 嵌合相手ハウジングは TABLE -1参照
プラグハウジングアッセンブリと支障なく嵌合すること
- 推奨取付ねじ : JIS B1115, B1122タッピングねじ
ねじ2種 呼び径 3 , 長さ:TABLE-3参照
- ねじ締め付トルク : 0.392N・m最大

-Z- 番から6mmの位置で測定
取扱い説明書 NO : 411-5928
適用端子は TABLE -2参照

コンタクト仕上識別記号 ; 表参照

-Z- 番から2mmの位置で測定

回路番号 : FIG.1 参照






FIG.1 回路番号
CIRCUIT NUMBER



6	5.6	Ø2.63	PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	24	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN × 24 (BRIGHT)	—//—	SPS GF17	NATURAL	3-1318853-4
6	5.6	Ø2.63	PAPER BOX タンボール箱	PLASTIC TUBE プラスチックチューブ	24	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN × 24 (BRIGHT)	—//—	SPS GF17	NATURAL	3-1318853-3
MARKING マーキング	WEIGHT (g) 質量	V	OUTER 分装	INNER 内装	TOTAL NUMBER OF CIRCUIT 回路総数	SOLDERING SIDE 半田付け側	CONTACT SIDE 接触部側	GOLD PLATED CIRCUIT NO (金めっき回路番号)	MATERIAL 材料	COLOR 色	PART NUMBER 製品型番
			PACKING STYLE 梱包形態			CONTACT FINISH コンタクト仕上			HOUSING ハウジング		

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN T. SHINOHARA 06OCT2015	TE Connectivity 025SERIES 24POSITION(PCB H-TYPE) CAP HOUSING ASSEMBLY			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: mm		0-PLC ±0.3 1-PLC ±0.1 2-PLC ±0.06 3-PLC ±0.025 4-PLC ±0.0001 ANGLES ±°	CHK H. YAMAGAMI 06OCT2015				
				APVD H. YAMAGAMI 06OCT2015				
				PRODUCT SPEC 108-5668				
				APPLICATION SPEC 114-5250				
MATERIAL CONTACT-BRASS HOUSING:SEE TABLE		FINISH SEE TABLE		WEIGHT SEE TABLE	SIZE A1	CAGE CODE 000779	DRAWING NO 3-1318853-3	RESTRICTED
Customer Drawing					SHEET 1 OF 2		REV A	

LOC		R1ST		REVISIONS					
J		P	LTR	DESCRIPTION		DATE	DWN	APVD	
			A	RELEASED		06OCT2015	TS	HY	
			A1	REVISED		ECR-16-003897	1MAR2016	TS	HY




TABLE -1	
POS 極数	PLUG HOUSING PART NO プラグハウジング 型番
24	1717112-3

TABLE -2		TERMINAL NO 端子型番	APPLICABLE WIRE RANGE (FEMALE) 適用電線 (メス)
SIGNAL 0.64mm	TIN	1674311-1	AVSS/CAVS/CAVUS/AVSSH-f 0.3-0.5mm ²

TABLE -3		
プリント基板板厚 (mm) THICKNESS OF PCB (mm)	1.2	1.6
固定用ねじ首下長さ (mm) NOMINAL LENGTH OF SCREW (mm)	5	6


TE Connectivity

025SERIES 24POSITION(PCB H-TYPE)
CAP HOUSING ASSEMBLY

SIZE
A1

SHEET 1 OF 2

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.1

2 PLC ±0.05

3 PLC ±0.025

4 PLC ±0.0001

ANGLES ±

FINISH

TE

TE Connectivity

NAME

025SERIES 24POSITION(PCB H-TYPE)
CAP HOUSING ASSEMBLY

SIZE

A2

CAGE CODE

-

DRAWING NO

3-1318853-3

RESTRICTED TO

-

SCALE

4:1

SHEET

2

OF

2

REV

A1