

Technical data sheet

Article number:
161-64204

HWPP16L2



Product Group	Helawrap cable cover
Product Family	HWPP in polypropylene
Material	Polypropylene (PP)
Colour	Black (BK)
Bundle Ø max.	16 mm
Bundle Ø min.	13 mm
Flammability	UL 94 HB
Nominal Ø	16 mm
Operating Temperature	-60 °C to +110 °C, intermittent +140 °C
Package Content packed in	pack
Pack Cont.	2 m
Specifications	ECE R 118-03 Abschnitt 6
Wall (WT)	0.8 mm



ECE R-118