

ENCLOSURE HARDWARE

LED INDICATORS

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING

SOLUTIONS

RESOURCES

FLP2FR12.0-SBC



Flexible Light Pipe Assembly, 2mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Flat Face Lens, 12.0in. Length, 3mm LED, Super Bi-Color Red/Green



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES	VALUE ADDED	CHECK STOCK
<ul style="list-style-type: none">Wavelength: 645nm / 568nm , Typical Intensity: 100mcd / 60mcd, Color: Red / GreenAssembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED4.2mm. Diameter Flat Face Lens CapFlexible Light Pipe Cable Customized Length-See Specification Sheet for More InfoMaterial: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 ClearRear Panel Mount Lens		

ecia
MEMBER

Enclosure Hardware

LED Indicators

LED Lighting

New Products

Locate a Distributor / Sales REP

Quality Assurance / RoHS

Product Info Center

Terms & Conditions

My Bivar

ESOP

100% Employee Owned