

Shop By Category

- Adapters
- Amphenol Connectors
- Audio Video Monitor Cables
- CAT-5e • CAT-6 • Telco Cables
- Coaxial Cables
- CX4 Cables • InfiniBand Cables
- DisplayPort Cables & Adapters
- D-Sub Cables • D-Sub Adapters
- Fiber Optic Patch Cables
- Fibre Channel & DIN Cables
- GPIB Cables (IEEE-488 Cables)
- HDMI Cables (High Speed HDMI)
- QSFP Cables • QSFP+ Cables
- QSFP+ Modules & Loopbacks
- SAS Cables • SATA Cables
- SCSI Cables • VHDCI Cables
- SFP Cables • SFP Modules
- SFP+ Cables • SFP+ Modules
- SFP28 Cables • QSFP28 Cables
- USB Cables

Shop By Application

- Get 25 Percent OFF High Speed
- Coax/D-Sub/CAT5e/6/6a SALE
- 25/100-Gigabit Ethernet Tech
- Custom Cables & Cable Kits
- Data Center Cable Solutions
- Home Theater AV Cable Center

More ways to Shop

- Hot Items
- New Items
- Overstock

SFP+ Cables • SFP+ Modules » SFP+ Cables (Direct Attach) »

5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (16.4 ft)

★★★★★ 1 Review Ask a question



Click for larger image

Amphenol 5m (16.4 ft) 10GbE SFP+ Direct Attach Copper Cables provide affordable 10-Gigabit Ethernet connectivity with any SFP+ enabled port. Each SFP+ cable utilizes an integrated 20-position "board-as-connector" design with zinc die-cast backshells for superior EMI performance and minimal insertion loss. Our 5m SFP+ cables are assembled with industry-leading 26 AWG twinaxial SKEWCLEAR® 2-pair wire; optimized for bandwidth-intense applications such as 10Gb Ethernet, Fibre Channel, InfiniBand, and SONET. Our cables are designed to the open-source SFF-8431 MSA standard in order to guarantee compatibility with the vast majority of SFP+ equipment on the market also based on that standard. For non-compliant SFP+ switches from HP, Cisco and Force10, we recommend using our fully-compatible SFP+ Optical Module (Part #: SF-10GSFPPLCL-000) instead.

Product Features:

- September Savings: 25% OFF SFP+/SFP28 with Coupon Code: HISPEED
- 5m (16.4ft) SFP+ 10GbE direct attach passive copper cable by Amphenol
- Our OEM Equivalent SFP+ Cables Connect to any Security-Free SFP+ Port
- 30-Days 100% Satisfaction Guarantee with No Restocking Fees
- 10G Ethernet, Fibre Channel, InfiniBand & SONET multi-platform support
- Zinc die-cast SFF-8431 SFP+ connectors with push-to-release latching
- High performance quad-shielded 26 AWG twinaxial SKEWCLEAR wire
- Built and tested by industry leader Amphenol Interconnect Products
- Low cross-talk and pair-to-pair skew
- Fully compliant to the latest SFP Plus MSA (multi-source agreement)
- Exceeds 10-Gigabit Ethernet and 10G Fibre Channel performance standards
- Enjoy a reduced power budget and lower port cost compared to optical
- Consumes only .15W per end - 20X less power than 10GBASE-T
- Featuring our latest Rev. 2.0 SFP+ PCB for enhanced performance
- Guaranteed to cross reference with the following brands:
- Tyco: 2032237-6 / 2032247-6 / 2053649-6
- Molex: 74752-3501
- Methode:DM-255-500
- Gore: SFN8200-5
- Woven: WV-CABLE-DA-SFP-5
- Amphenol: SFPP2XPASS-005
- Interested in larger volumes or custom lengths? Call 1-866-223-2860

Item#	Color	Length	Qty 1-50	Qty >50	Availability	Order Qty
SF-SFPP2EPASS-005		5m (16.4ft)	\$	\$	In Stock	

Add all entered quantities to cart - > Add To Cart

Same Day Shipping

Product Diagram Available. Please click [here](#) to download.



Similar Products

0.5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (1.6 ft)



10m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (32.8 ft)



1m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (3.3 ft)



2m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (6.6 ft)



3m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (9.8 ft)



7m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (23 ft)



8.5m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (27.9 ft)



8m SFP+ Cable - Amphenol 10GbE SFP+ Direct Attach Copper Cable (26.2 ft)



