



Catalog No. 18RAD-18377

Description: NYL FLLY INS FEM-187 DISC, 22-18

UPC No 786210819228

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Nylon-Insulated Female Disconnect, Length .89 Inches, Width .30 Inches, Maximum Insulation .150, Tab Size .187x.032 Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

Descriptors	
Category	Wire terminal disconnect
Special Features	Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.
Specifications	
Material	Brass
Finish	Tin Plated
Color	Red
Insulation	Nylon/Polyamide
Classifications	
Brand Name	Sta-Kon
Standard	UL E66716 UL E66716
Compliance and Certifications	
RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially isolated
Colour insulation	Red
Material insulation	PA
Material	Copper
AWG-range	22-18