

Pushbutton, 18.2 mm, screw terminal, momentary contact function,
1 NC + 1 NO, bezel black



Description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A

technical data

> general		direct links
Bezel color	black	> RAFI eCatalog
Property of bezel / mushroom	opaque	
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	85 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	90 °C	
illuminated	No	
Packaging	Box	
Packaging unit	100 pcs.	
net weight	16 g	
Operating life	50,000 cycles	
B10	65,000 cycles	
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap	
Minimum order quantity (MOQ)	100 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
country of origin	HU	
> mounting diameters		
Outside dimension, length	22 mm	
Outside dimension, width	22 mm	
Outside dimension, height	44.5 mm	
Mounting hole	18.2 mm	
Mounting depth	34 mm	
Installation height	10.5 mm	
> mechanical data		
Actuation function	momentary contact function	
Operating force, min.	9.5 N	
Operating travel, max.	5 mm	

Contact function	1 NC + 1 NO
Contact system	Bridge-sliding contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal
> electrical data	
Rated voltage, max.	250 V
Rated current, max.	2 A