

Power Matters.™

Home > JANS2N6678T1 (#76047)

Products

- Product Directory
- Applications Directory
- Parametric Search

JANS2N6678T1 (#76047)

Overview

Diagrams

Electrical Rating	Symbol	Min	Typ	Max	Unit
DC Current Gain	HFE	8.00		20.00	
Turn Off Time (nS)	t _{off}			3000.00	ns

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Collector Current (dc)	I _C			15.00	A
Collector-Emitter Voltage (Base Open)	V _{CEO}			400.00	V
Junction Temperature (°C)	T _J			200.00	°C

This part can be found in the following product categories:

- Non-Radiation Hardened Devices > Transistors > BJT(BiPolar Junction Transistor) > NPN Transistor
- Discretes > Transistors > BJT(BiPolar Junction Transistor) > NPN Transistor

Related Links

- Technical support
- Sales Contacts
- Available Stock
- Sales Contacts
- RFQ/Samples