

FED10S1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ End Sections

General Information

Extended Product Type:	FED10S1
Product ID:	1SNA215999R2100
EAN:	3472592159997
Catalog Description:	FED10S1 End Sections Grey
Long Description:	FED10S1 - End Sections - Grey - 2mm Spacing.

Ordering

Color:	Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Width:	2 mm
Product Net Height:	82 mm
Product Net Depth / Length:	43.7 mm
Product Net Weight:	3.4 g

Technical

Spacing:	2 mm
Function:	End Sections
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	D6/10.SNBTB

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Environmental Information:	1SND220090E1000
RoHS Information:	1SND230478F0202

Classifications

Object Classification Code:	X
------------------------------------	---

ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	155 mm
Package Level 1 Depth / Length:	200 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.068 kg
Package Level 1 EAN:	3472592159997
Package Level 2 Units:	300 piece
Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Product Packing Type:	Bag

