


FSK-22A-22 Product Details


Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri


FSK-22A-22 (6-1437212-4)

TE Part Number: 6-1437212-4

Active
[Add to Part List](#)

FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 2.54 mm Centerline
- Kapton Insulation Material
- Insulation Length = 50.80 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [None Available](#)

Catalog Pages/Data Sheets:

- [None Available](#)

Product Specifications:

- [None Available](#)

Application Specifications:

- [None Available](#)

Instruction Sheets:

- [None Available](#)

CAD Files:

- [None Available](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product View](#)
- [Product View](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Insulation Material](#) = Kapton
- [Number of Conductors](#) = 22

Electrical Characteristics:

- Current Rating (Amps.) = 3
- Impedance (Ω) = 117
- Voltage Rating (VAC) = 300

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- [Insulation Length \(mm \[in\]\)](#) = 50.80 [2.000]

Configuration Related Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +150 [-40 - +302]

Other:

- Brand = Tyco Electronics