



Pushing Performance

D-Sub, MA AWG 20-24 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 8576
Specification	D-Sub, MA AWG 20-24 crimp cont
HARTING eCatalogue	https://b2b.harting.com/09670008576

Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm ²
Conductor cross-section	AWG 24 ... AWG 20
Contact resistance	≤10 mΩ
Stripping length	4 mm
Performance level	1
	acc. to CECC 75301-802

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors