





REV.	DATE	DESCRIPTION
NC	04/03/05	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
8						DRAWN	G.R.S.					04/03/05
7						CHECKED			PART DESCRIPTION SMB CRIMP JACK (RG-58/U, 58B/U CABLE)			
6						ISSUED						
5	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1		PART NO. 142330			
3	CONTACT PIN	BRASS	GOLD	1	CAD FILE C:/142/142330.DWG			DWG. NO. 142330.DWG				
2	INSULATOR	TEFLON	NATURAL	1								
1	BODY	BRASS	GOLD	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								